Sharpener

Optional Accessory 32BL Installing the motor can do up-down swing motion AC Motor/ AC Speed Controller



Standard Accessaries for EY-32A Standard Accessaries for EY-328 # 1 Cam for single fute chamfering tool # 1 Cam for single fute chamfering tool

# 2 Cam for drill	#2 Cam for drill
#3 Cam for 3 flutes chamfering tool	#3 Cam for 3 flutes chamfering tool
#4 Cam for 4 flutes tap	#4 Cam for 4 flutes tap
Automatic Centering 6-jaw Chuck	Automatic Centering 6-jaw Chuck
Flange with Counter Weight	Flange with Counter Weight
Manual Lubricator	Manual Lubricator
Morse Taper Sleeve MT2, MT3	Morse Taper Sleeve MT2, MT3
Quartz Working Light	Quartz Working Light
Operation Manual	Operation Manual
Tool box	Tool box
Precision Ball Screw for X, Y-axis Ø16mm	Precision Ball Screw for X, Y-axis Ø16mm
Sealed Stand	Whole Water Collecting Half Cover Stand
Grinding Wheel	CBN Grinding Wheel Ø 150 x 31.75 x 201
	CBN Grinding Wheel Ø 125 x 31.75 x 2.0
	Cooling Motor with Automatic Circulating

European Electrical Control Box

Automatic Power Cut Protective Device for Leakage Red Emergency Button

Specialized for HSS Material Use EY-32A(Optional Accessories) EY-32B(Standard Accessories) CBN Ploygon-type 150*20T*31.75mm CBN Disk-type 125*2T*31.75 mm





Specialized for Tungsten Steel Material Use(Optional Accessories) SDC Ploygon-type 150*20T*31.75 mm SDC Disk-type 125*2T*31.75 mm





EY-32B Precision Drill Sharpener



(Manual lubrication system for slideway and ball screw.)

Can install on EY-32A and EY-32B

Optional Accessories
32C Knife Edge Grinding Accessory



Spiral grinding (Air-bearing device)

 Function: Grind the outside diameter of end milling cutter, side milling cutter, reamer and outside diameter of drill.

- product feature: Frictionless design, when the main shaft roundness kept within 0.005mm, it can rotate quickly and operate easily, cutter setting can be done under 2 minutes.
- Pneumatic mail shaft is manufactured through heat treatment, chrome plated and ground on the surface which makes if free from rusty and precision lasting. The first edge of sharpener and second clearance angle be set very cuickly.